


## FVG9401<sup>+</sup> and KA9121<sup>+</sup> with new safety functions

The control units of the FVG9401 and KA9121 are from now on equipped with extended safety functions.

- 2 channel emergency stop
- 2 channel STO function
- optional SLS for setting

Please observe the chapter „Safety functions“ in the manual prior to commissioning of the device.

Wiring example:



**Attention:** The configuration of X17 has been changed compared to older devices. In case the option SLS is not existing X15 must not be wired.

Additional wiring examples are available in the manual.

The function SLS requires an actuator with a safety-related encoder. Therefore a corresponding actuator is necessary to execute SLS.

**Setting operations with SLS is not possible with older actuators of the same series.**